

GLORIETA 08 Design Guide








Profile & Dimensions





Ordering Information



GLOR-08-CHAN-XXX-6.5 XXX=SIL (Silver), BLK (Black) Anodized Aluminum Extrusion, available in 6.5' lengths



GLOR-08-LNS-SIL-XXX-XXX XXX= DIF (Diffuser), BLK (Black) XXX (unit in feet) = 10, 50, 100 Silicone Lens Roll



GLOR-08-EC-XXX-01 XXX= WHT (White), BLK (Black) Solid End Cap



GLOR-08-EC-XXX-02 XXX= WHT (White), BLK (Black) Powerfeed End Cap

Diode Visibility





Diffused lens

Black lens



Installation



Before installatino make sure extrusion is free of any defects and clean



Install extrusion to the base of desired location



Stick mesh-tape on extrusion and drywall evenly divided on both surfaces



Apply spakle eveny across both surface to desired look and let dry



After drying - finish with paint coat

Note: Glorieta 08 is a bendable extrusion and can be formed to curved surfaces



Tivoli, LLC. reserves the right to modify this specification without prior notice.